


## DCL with Schrader valve - Filter Driers

The new Danfoss capillary tube filter driers include a Schrader valve, making servicing the system easy and convenient, and convertible outlet for fitting on capillary tube or ¼ inch system connection.

Thanks to the solid core, Danfoss ELIMINATOR® filter driers offer exceptional drying capacity to protect the system against harmful acids and moisture.



Features

DCL w/Schrader



### Facts

#### Applications:

- Traditional refrigeration
- Air conditioning units
- Transport refrigeration

#### • Connections:

- Inlet: ¼ inch solder and ¼ inch service port
- Outlet: Capillary tube outlet can be trimmed down to ¼ inch


- Refrigerants: R-22, R-32, R-134a, R-404A, R-410A, R-407C/F, R-23, R-600, R-600a, R-1234yf, R-1234ze,

R-290, R-452A, R-444B, R-449A, R-448A, R-450A, R-507. For other refrigerants, please contact Danfoss.

- Available with 1.5, 3, and 5 cubic inch solid core volumes
- 80% molecular sieve and 20% activated alumina core

## Technical data and ordering

### DCL with Schrader valve - Filter Drier



Danfoss Type	Connection inlet (in.)/ outlet	Max. working pressure (psig)	Drying capacity (lbs. of refrigerant)										Liquid capacity (tons)					Danfoss Code No.
			R-134a		R-404A		R-22		R-407C		R-410A		R-134a	R-404C	R-22	R-407C	R-410A	
			75°F	125°F	75°F	125°F	75°F	125°F	75°F	125°F	75°F	125°F						
DCL 1.52/ CAPsV	¼/capillary tube	667	5.2	4.8	5.5	5.2	5.3	4.9	5.1	4.7	4.7	4.2	1.0	0.7	1.1	1.0	1.0	<b>023Z8261</b>
DCL 032/ CAPsV	¼/capillary tube	667	8.4	7.7	8.8	8.3	8.5	7.8	8.2	7.6	7.6	6.8	1.2	0.8	1.3	1.2	1.2	<b>023Z5174</b>
DCL 052/ CAPsV	¼/capillary tube	667	13.5	12.4	14.1	13.4	13.6	12.5	13.1	12.1	12.3	10.9	1.2	0.8	1.3	1.2	1.2	<b>023Z5181</b>